



IndorTec® FLEXDRAIN-HD




Sicher besser.
GUTJAHR


izonet
HIDROIZOLACIONI SISTEMI


IZONET D.O.O.
ADRESA 1: Jovana Popovića - Lipovca b.b., blok IX (ATC Top Plus), 81000, Podgorica
ADRESA 2: Kovačko polje b.b., 85330, Kotor
E-MAIL: team@izonet.net
MOB 1: +382 68 17 88 44
MOB 2: +382 68 42 49 17
TEL/FAX: +382 32 32 66 96
www.izonet.net



1. ARDEX P 51 primer
2. ARDEX S 1-K waterproofing layer
3. ARDEX FB 9 L adhesive for ceramic/stone
4. ceramic/stone paving
5. IndorTec® FLEXDRAIN-HD line drain
6. flange of the drain

 Unique, flexible and ultra-flat shower gully system, which has two drainage levels and the innovative seal collar, attached by the manufacturer, which is excellent for safe bonding with waterproofing layer.

 Drain away water from stone or ceramic paving and drainage it below paving.



- Drainage prevents damage caused by seepage water accumulation and prolongs work life of waterproof layer and prevents the appearance of the stains on paving.


- Maximum flexibility reduces the need for different versions of the gully.

- The reversible cover can be used both as a holder for tile and a stainless steel cover.


1. Reversible part which can be used as holder for tile or stainless cover
2. Second drainage level: Stainless steel drain frame with covered drainage slits
3. Stainless steel gully body with seal collar attached on site, with 11 mm narrow adhesive flange
4. Ultra-shallow installation height



- The seal collar, attached by the manufacturer, with its narrow adhesive flange enables universal use even in corner and wall areas.



- It is easily cleaned because every part of the gully can be simply removed.



- Available in three lengths: 750 mm / 950 mm/1150 mm and two frame height: 11 mm for ceramic and mosaic, 22 mm for natural stone.

Easy height adjustment:

1. Pull off support clip
2. Slide the height adjuster to the middle and adjust the height (6-15 mm)
3. Slide the height adjustment apart and fit the support clip.